

Han B Protect Cover Die Cast for Hood Co



Part number	09 30 010 5427
Specification	Han B Protect Cover Die Cast for Hood Co
HARTING eCatalogue	https://b2b.harting.com/09300105427

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Protection cover
Description of hood/housing	for cable to cable housing Metal With fixing cord
Type	Low construction High construction

Version

Locking type	Double locking lever
Size	10 B
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	52 g
Country of origin	Germany
Customs tariff number	85389099