

Han 10B-AK-LB-Dichtung



Part number	09 30 010 5432
Specification	Han 10B-AK-LB-Dichtung
HARTING eCatalogue	https://b2b.harting.com/09300105432

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Protection cover
Description of hood/housing	for hoods Metal With fixing cord
Type	Low construction High construction

Version

Locking type	Single locking lever
Han-Easy Lock [®]	Yes
Size	10 B
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	77 g
Country of origin	Germany
Customs tariff number	85389099