

Han B Protect Cover Die Cast for Hood PG



Part number	09 30 024 5422	
Specification	Han B Protect Cover Die Cast for Hood PG	
HARTING eCatalogue	https://b2b.harting.com/09300245422	
Identification		
Category	Hoods/Housings	
Series of hoods/housings Han [®] B		
Type of hood/housing	Protection cover	
Description of hood/ housing	for hoods Metal With fixing cord	
Туре	Low construction High construction	

Version

Locking type	Double locking lever
Han-Easy Lock [®]	Yes
Size	24 B
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant

Page 1 / 2 | Creation date 2018-09-07 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
Commercial data	
Packaging size	1
Net weight	118 g
Country of origin	Germany
Customs tariff number	85389099