

Han M Protect Cover Die Cast for Base



Part number	09 37 003 5405
Specification	Han M Protect Cover Die Cast for Base
HARTING eCatalogue	https://b2b.harting.com/09370035405

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Protection cover
Description of hood/ housing	for bulkhead mounted housings
	for surface mounted housings
	for cable to cable housing
	Metal
	With fixing cord

Version

Locking type	Single locking lever
Size	3 A
Field of application	Hoods/housings for rough environments
Details	for mounted female insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

Material properties

Material (seal)	FPM
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	23.8 g
Country of origin	Romania
Customs tariff number	85389099
