

Han 16M-Metal Cover-DL-Seal-for Hood



Part number	09 37 016 5402
Specification	Han 16M-Metal Cover-DL-Seal-for Hood
HARTING eCatalogue	https://b2b.harting.com/09370165402

Identification

Category	Hoods/Housings	
Series of hoods/housings Han® M		
Type of hood/housing	Protection cover	
Description of hood/ housing	for hoods Metal With fixing cord	
Туре	Low construction High construction	

Version

Locking type	Double locking lever
Size	16 B
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X
	12

Material properties

Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	127.1 g
Country of origin	Germany
Customs tariff number	85389099