

Han 3HPR-C-TL-w/o cord- black chrome



Part number	09 40 003 5401
Specification	Han 3HPR-C-TL-w/o cord- black chrome
HARTING eCatalogue	https://b2b.harting.com/09400035401

Identification

Category	Hoods/Housings	
Series of hoods/housings Han® HPR		
Type of hood/housing	Protection cover	
Description of hood/ housing	for bulkhead mounted housings	
	for surface mounted housings	

Version

Locking type	Toggle locking
Size	3 A
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
	IP68
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Product data sheet 09 40 003 5401 Han 3HPR-C-TL-w/o cord- black chrome



Commercial data

Packaging size	10
Net weight	46.9 g
Country of origin	China
Customs tariff number	8538900000