

Han 3HPR-C-TL-with cord-black chrome



Part number	09 40 003 5402
Specification	Han 3HPR-C-TL-with cord-black chrome
HARTING eCatalogue	https://b2b.harting.com/09400035402

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] HPR
Type of hood/housing	Protection cover
Description of hood/ housing	for bulkhead mounted housings for surface mounted housings With fixing cord

Version

Locking type	Toggle locking
Size	3 A
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	49 g
Country of origin	China
Customs tariff number	8538900000