

## Han 3HPR-C-SL-W/O cord-black chrome



Part number	09 40 003 5411
Specification	Han 3HPR-C-SL-W/O cord-black chrome
HARTING eCatalogue	<a href="https://b2b.harting.com/09400035411">https://b2b.harting.com/09400035411</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> HPR
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings

### Version

Locking type	Screw locking
Size	3 A
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	2 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances No

---

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

---

## Commercial data

Packaging size	10
Net weight	46.7 g
Country of origin	China
Customs tariff number	8538900000

---