

# Han 6HPR hood cover screw locking



Part number	09 40 006 5414	
Specification	Han 6HPR hood cover screw locking	
HARTING eCatalogue	https://b2b.harting.com/09400065414	
Identification		
Category	Hoods/Housings	
Series of hoods/housingsHan <sup>®</sup> HPR		
Type of hood/housing	Protection cover	
Description of hood/ housing	for hoods	

## Version

Locking type	Screw locking
Size	6 B
Field of application	Hoods/housings for harsh outdoor environments

## **Technical characteristics**

Limiting temperature	-40 +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e

Page 1 / 2 | Creation date 2018-08-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



## Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

#### Commercial data

Packaging size	1
Net weight	109.4 g
Country of origin	China
Customs tariff number	8538900000