

# Han 10 HPR Cover Screw Locking



Part number	09 40 010 5411
Specification	Han 10 HPR Cover Screw Locking
HARTING eCatalogue	https://b2b.harting.com/09400105411

#### Identification

Category	Hoods/Housings
Series of hoods/housings Han® HPR	
Type of hood/housing	Protection cover
Description of hood/ housing	for bulkhead mounted housings
	for surface mounted housings

#### Version

Locking type	Screw locking
Size	10 B
Field of application	Hoods/housings for harsh outdoor environments

#### Technical characteristics

Limiting temperature	-40 +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68
	IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No



## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
	C3A-C22.2 NO. 102.3 ECB10.L233070

## Commercial data

Packaging size	1
Net weight	146.9 g
Country of origin	Germany
Customs tariff number	85389099