

Han-Yellock 30 cover for hood



Part number	11 12 300 5451
Specification	Han-Yellock 30 cover for hood
HARTING eCatalogue	https://b2b.harting.com/11123005451

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Protection cover
Description of hood/ housing	for carrier hoods With fixing cord Thermoplastic

Version

Size	Han-Yellock® 30
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

IEC 61984

Commercial data

Packaging size	1
Net weight	31.65 g
Country of origin	Germany
Customs tariff number	85389099