

Han-Yellock cover for BH housing - 60mm



Part number	11 12 600 5401
Specification	Han-Yellock cover for BH housing - 60mm
HARTING eCatalogue	https://b2b.harting.com/11126005401

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings Thermoplastic

Version

Size	Han-Yellock® 60
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

Commercial data

Packaging size	1
Net weight	61.6 g
Country of origin	Germany
Customs tariff number	85389099