

Han-Yellock 10 cover f. hood



Part number	11 20 003 5456
Specification	Han-Yellock 10 cover f. hood
HARTING eCatalogue	https://b2b.harting.com/11200035456

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Protection cover
Description of hood/ housing	for hoods Thermoplastic

Version

Size	Han-Yellock® 10
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C

Material properties

Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	10
----------------	----



Pushing Performance

Commercial data

Net weight	9.95 g
Country of origin	Germany
Customs tariff number	85389099
