

Han INOX 3A Cover for Female in Housing



Part number	19 44 003 5425
Specification	Han INOX 3A Cover for Female in Housing
HARTING eCatalogue	https://b2b.harting.com/19440035425

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings for cable to cable housing Metal With fixing cord

Version

Locking type	Single locking lever
Size	3 A
Field of application	Hoods/housings for harsh environments
Details	for mounted female insert or for mounted Han-Brid® insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	25.5 g
Country of origin	Germany
Customs tariff number	85389099