

## Protect cover Han-INOX for hood



Part number	19 44 310 5422
Specification	Protect cover Han-INOX for hood
HARTING eCatalogue	<a href="https://b2b.harting.com/19443105422">https://b2b.harting.com/19443105422</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Protection cover
Description of hood/ housing	for hoods Metal With fixing cord

### Version

Locking type	Single locking lever
Size	10 B
Field of application	Hoods/housings for harsh environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	264.2 g
Country of origin	Germany
Customs tariff number	85389099