

Han 3HPR-HSM angled



Part number	09 40 003 0902
Specification	Han 3HPR-HSM angled
HARTING eCatalogue	https://b2b.harting.com/09400030902

Identification

Category	Hoods/Housings
Series of hoods/housings Han® HPR	
Type of hood/housing	Adapter
Description of hood/ housing	Open bottom
	for assembly of bulkhead mounted bulkhead mounted position

Version

Size	3 A
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	96.4 g
Country of origin	Germany
Customs tariff number	85389099