

## Han HC-AX-PE-Kontaktstift



Part number	09 11 000 6156
Specification	Han HC-AX-PE-Kontaktstift
HARTING eCatalogue	<a href="https://b2b.harting.com/09110006156">https://b2b.harting.com/09110006156</a>

### Identification

Category	Contacts
Series	TC 350
Type of contact	Axial screw contact
Description of the contact	PE contact

### Version

Gender	Male
--------	------

### Technical characteristics

Conductor cross-section	35 ... 70 mm <sup>2</sup>
Operating current	≤350 A
Contact resistance	≤0.2 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	19 ... 20 mm
Tightening torque	8 Nm @ 35 mm <sup>2</sup>
	10 Nm @ 50 mm <sup>2</sup>
	12 Nm @ 70 mm <sup>2</sup>
Mating cycles	≥500

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight 6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

## Commercial data

Packaging size	1
Net weight	133.72 g
Country of origin	Germany
Customs tariff number	85359000