

## Han TC100 female contact ax (10-25mm<sup>2</sup>)AG



Part number	09 11 000 6212
Specification	Han TC100 female contact ax (10-25mm <sup>2</sup> )AG
HARTING eCatalogue	<a href="https://b2b.harting.com/09110006212">https://b2b.harting.com/09110006212</a>

### Identification

Category	Contacts
Series	TC 100
Type of contact	Axial screw contact

### Version

Gender	Female
--------	--------

### Technical characteristics

Conductor cross-section	10 ... 25 mm <sup>2</sup>
Operating current	≤100 A
Contact resistance	≤0.3 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	13 mm
Tightening torque	6 Nm @ 10 mm <sup>2</sup>
	6 Nm @ 16 mm <sup>2</sup>
	7 Nm @ 25 mm <sup>2</sup>
Mating cycles	≥500

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Pushing Performance

## Material properties

REACH SVHC substances	Lead
-----------------------	------

---

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	10
Net weight	20.86 g
Country of origin	Germany
Customs tariff number	85366990

---