

Han TC250 female contact 50mm²



Part number	09 11 000 6228
Specification	Han TC250 female contact 50mm ²
HARTING eCatalogue	https://b2b.harting.com/09110006228

Identification

Category	Contacts
Series	TC 250
Type of contact	Crimp contact

Version

Gender	Female
--------	--------

Technical characteristics

Conductor cross-section	50 mm ²
Operating current	≤250 A
Contact resistance	≤0.3 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	22 mm
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

	IEC 61984
--	-----------

Commercial data

Packaging size	1
Net weight	48.4 g
Country of origin	Germany
Customs tariff number	85359000