

Han TC70 Buchsenkontakt 16sqmm



Part number	09 11 000 6232
Specification	Han TC70 Buchsenkontakt 16sqmm
HARTING eCatalogue	https://b2b.harting.com/09110006232

Identification

Category	Contacts
Series	TC 70
Type of contact	Crimp contact

Version

Gender	Female
--------	--------

Technical characteristics

Conductor cross-section	16 mm ²
Operating current	≤70 A
Contact resistance	≤0.5 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	15.5 mm
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

IEC 61984

Commercial data

Packaging size	10
Net weight	9.28 g
Country of origin	Germany
Customs tariff number	85366990