

## Han TC100 female contact 35 mm<sup>2</sup>



Part number	09 11 000 6235
Specification	Han TC100 female contact 35 mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09110006235">https://b2b.harting.com/09110006235</a>

### Identification

Category	Contacts
Series	TC 100
Type of contact	Crimp contact

### Version

Gender	Female
--------	--------

### Technical characteristics

Conductor cross-section	35 mm <sup>2</sup>
Operating current	≤100 A
Contact resistance	≤0.3 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	16 mm
Mating cycles	≥500

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

## Specifications and approvals

IEC 61984
-----------

## Commercial data

Packaging size	10
Net weight	21.32 g
Country of origin	Germany
Customs tariff number	85359000