

## Han TC350 Buchsenkontakt 50mm<sup>2</sup>



Part number	09 11 000 6241
Specification	Han TC350 Buchsenkontakt 50mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09110006241">https://b2b.harting.com/09110006241</a>

### Identification

Category	Contacts
Series	TC 350
Type of contact	Crimp contact

### Version

Gender	Female
--------	--------

### Technical characteristics

Conductor cross-section	50 mm <sup>2</sup>
Operating current	≤350 A
Contact resistance	≤0.3 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	28 mm
Mating cycles	≥500

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

## Commercial data

Packaging size	1
Net weight	72.68 g
Country of origin	Germany
Customs tariff number	85359000