

Han TC650 Buchsenkontakt 240mm²



Part number	09 11 000 6268
Specification	Han TC650 Buchsenkontakt 240mm ²
HARTING eCatalogue	https://b2b.harting.com/09110006268

Identification

Category	Contacts
Series	TC 650
Type of contact	Crimp contact

Version

Gender	Female
--------	--------

Technical characteristics

Conductor cross-section	240 mm ²
Operating current	≤650 A
Contact resistance	≤0.3 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	46 mm
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

Commercial data

Packaging size	1
Net weight	222.82 g
Country of origin	Germany
Customs tariff number	85359000
