

## Han D F CRIMP CONTACT Fe(Au) 0,14-0,37



Part number	09 15 000 6271
Specification	Han D F CRIMP CONTACT Fe(Au) 0,14-0,37
HARTING eCatalogue	<a href="https://b2b.harting.com/09150006271">https://b2b.harting.com/09150006271</a>

### Identification

Category	Contacts
Series	Han D <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Female
--------	--------

### Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Operating current	≤10 A
Contact resistance	≤1 mΩ
Stripping length	8 mm

### Material properties

Material (contacts)	Iron
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

## Commercial data

Packaging size	25
Net weight	0.68 g
Country of origin	Germany
Customs tariff number	85366990