

Han E Female Contact 26-22AWG Constantan



Part number	09 33 000 6263
Specification	Han E Female Contact 26-22AWG Constantan
HARTING eCatalogue	https://b2b.harting.com/09330006263

Identification

Category	Contacts
Series	Han E®
Type of contact	Crimp contact

Version

Gender	Female
Contact identification	acc. to IEC 60584 type J

Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm ²
Conductor cross-section	AWG 26 ... AWG 22
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

Commercial data

Packaging size	25
Net weight	1.74 g
Country of origin	Germany
Customs tariff number	85366990
