

## Han-Yellock F-c 2.5mm<sup>2</sup> (Ag)



Part number	11 05 000 6206
Specification	Han-Yellock F-c 2.5mm <sup>2</sup> (Ag)
HARTING eCatalogue	<a href="https://b2b.harting.com/11050006206">https://b2b.harting.com/11050006206</a>

### Identification

Category	Contacts
Series	Han-Yellock <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Female
--------	--------

### Technical characteristics

Conductor cross-section	2.5 mm <sup>2</sup>
Conductor cross-section	AWG 14
Operating current	≤20 A
Contact resistance	≤2 mΩ
Stripping length	6.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

## Specifications and approvals

	IEC 61984
--	-----------

## Commercial data

Packaging size	100
Net weight	0.67 g
Country of origin	Germany
Customs tariff number	85366990