

Han-Yellock F-c 3mm² (Ag)



| | |
|--------------------|---|
| Part number | 11 05 000 6207 |
| Specification | Han-Yellock F-c 3mm ² (Ag) |
| HARTING eCatalogue | https://b2b.harting.com/11050006207 |

Identification

| | |
|-----------------|--------------------------|
| Category | Contacts |
| Series | Han-Yellock [®] |
| Type of contact | Crimp contact |

Version

| | |
|--------|--------|
| Gender | Female |
|--------|--------|

Technical characteristics

| | |
|-------------------------|-------------------|
| Conductor cross-section | 3 mm ² |
| Conductor cross-section | AWG 12 |
| Operating current | ≤20 A |
| Contact resistance | ≤2 mΩ |
| Stripping length | 6.5 mm |

Material properties

| | |
|-----------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Silver plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|----------------|------------|
| Specifications | EN 60664-1 |
|----------------|------------|



Pushing Performance

Specifications and approvals

| | |
|--|-----------|
| | IEC 61984 |
|--|-----------|

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 100 |
| Net weight | 0.68 g |
| Country of origin | Germany |
| Customs tariff number | 85366990 |