

Han TC250 PE male contact 35mm²



Part number	09 11 000 6104
Specification	Han TC250 PE male contact 35mm ²
HARTING eCatalogue	https://b2b.harting.com/09110006104

Identification

Category	Contacts
Series	TC 250
Type of contact	Crimp contact
Description of the contact	PE contact

Version

Gender	Male
--------	------

Technical characteristics

Conductor cross-section	35 mm ²
Operating current	≤250 A
Contact resistance	≤0.3 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	20 mm
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	1
Net weight	44.54 g
Country of origin	Germany
Customs tariff number	85359000