


Han TC70 Stiftkontakt 10sqmm



Part number	09 11 000 6131
Specification	Han TC70 Stiftkontakt 10sqmm
HARTING eCatalogue	https://b2b.harting.com/09110006131

Identification

Category	Contacts
Series	TC 70
Type of contact	Crimp contact

Version

Gender	Male
--------	------

Technical characteristics

Conductor cross-section	10 mm ²
Operating current	≤70 A
Contact resistance	≤0.5 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	15.5 mm
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

	IEC 61984
--	-----------

Commercial data

Packaging size	10
Net weight	8.93 g
Country of origin	Germany
Customs tariff number	85359000