

Han D M Crimpkontakt 0,14-0,37 mm² CuNi



Part number	09 15 000 6161
Specification	Han D M Crimpkontakt 0,14-0,37 mm² CuNi
HARTING eCatalogue	https://b2b.harting.com/09150006161

Identification

Category	Contacts
Series	Han D [®]
Type of contact	Crimp contact

Version

Gender	Male	
--------	------	--

Technical characteristics

Conductor cross-section	0.14 0.37 mm²
Conductor cross-section	AWG 26 AWG 22
Operating current	≤10 A
Contact resistance	≤1 mΩ
Stripping length	8 mm

Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1
Specifications	IEC 61984

Commercial data

Packaging size 25	
-------------------	--

Product data sheet 09 15 000 6161 Han D M Crimpkontakt 0,14-0,37 mm² CuNi



Commercial data

Net weight 0.7 g

Country of origin	Germany
Customs tariff number	85366990