

Han D M Crimpkontakt 0,14-0,37mm² Fe



Part number	09 15 000 6171
Specification	Han D M Crimpkontakt 0,14-0,37mm ² Fe
HARTING eCatalogue	https://b2b.harting.com/09150006171

Identification

Category	Contacts
Series	Han D [®]
Type of contact	Crimp contact

Version

Gender	Male
--------	------

Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm ²
Conductor cross-section	AWG 26 ... AWG 22
Operating current	≤10 A
Contact resistance	≤1 mΩ
Stripping length	8 mm

Material properties

Material (contacts)	Iron
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

Commercial data

Packaging size	25
Net weight	0.64 g
Country of origin	Germany
Customs tariff number	85366990