

## Han C-male contact-c 10mm<sup>2</sup>



Part number	09 32 000 6109
Specification	Han C-male contact-c 10mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09320006109">https://b2b.harting.com/09320006109</a>

### Identification

Category	Contacts
Series	Han <sup>®</sup> C
Type of contact	Crimp contact

### Version

Gender	Male
--------	------

### Technical characteristics

Conductor cross-section	10 mm <sup>2</sup>
Conductor cross-section	AWG 8
Operating current	≤40 A
Contact resistance	≤1 mΩ
Stripping length	12 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

## Specifications and approvals

	IEC 61984
--	-----------

## Commercial data

Packaging size	25
Net weight	3.24 g
Country of origin	Germany
Customs tariff number	85366990