

Han E M Crimp Conatct Ag AWG 12



| | |
|--------------------|---|
| Part number | 09 33 000 6106 |
| Specification | Han E M Crimp Conatct Ag AWG 12 |
| HARTING eCatalogue | https://b2b.harting.com/09330006106 |

Identification

| | |
|-----------------|---------------|
| Category | Contacts |
| Series | Han E® |
| Type of contact | Crimp contact |

Version

| | |
|------------------------|-------------|
| Gender | Male |
| Contact identification | Wide groove |

Technical characteristics

| | |
|-------------------------|-------------------|
| Conductor cross-section | 3 mm ² |
| Conductor cross-section | AWG 12 |
| Operating current | ≤16 A |
| Contact resistance | ≤1 mΩ |
| Stripping length | 7.5 mm |

Material properties

| | |
|-----------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Silver plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|----------------|------------|
| Specifications | EN 60664-1 |
|----------------|------------|



Pushing Performance

Specifications and approvals

| | |
|--|-----------|
| | IEC 61984 |
|--|-----------|

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 100 |
| Net weight | 1.3 g |
| Country of origin | Germany |
| Customs tariff number | 85366990 |