

Han E relay contact-c 0,75-1mm² (Ag)



Part number	09 33 000 6109
Specification	Han E relay contact-c 0,75-1mm ² (Ag)
HARTING eCatalogue	https://b2b.harting.com/09330006109

Identification

Category	Contacts
Series	Han E [®]
Type of contact	Crimp contact
Description of the contact	Relay contact

Version

Gender	Male
--------	------

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section	AWG 18
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

	IEC 61984
--	-----------

Commercial data

Packaging size	100
Net weight	1.19 g
Country of origin	Germany
Customs tariff number	85366990