

## Han E M Crimp Contact Au WG 4 mm



Part number	09 33 000 6119
Specification	Han E M Crimp Contact Au WG 4 mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09330006119">https://b2b.harting.com/09330006119</a>

### Identification

Category	Contacts
Series	Han E®
Type of contact	Crimp contact

### Version

Gender	Male
Contact identification	No groove

### Technical characteristics

Conductor cross-section	4 mm <sup>2</sup>
Conductor cross-section	AWG 12
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

## Specifications and approvals

	IEC 61984
--	-----------

## Commercial data

Packaging size	100
Net weight	1.31 g
Country of origin	Germany
Customs tariff number	85366990