

## Han E Male Contact 20 Awg Constantan



Part number	09 33 000 6162
Specification	Han E Male Contact 20 Awg Constantan
HARTING eCatalogue	<a href="https://b2b.harting.com/09330006162">https://b2b.harting.com/09330006162</a>

### Identification

Category	Contacts
Series	Han E®
Type of contact	Crimp contact

### Version

Gender	Male
Contact identification	acc. to IEC 60584 type J

### Technical characteristics

Conductor cross-section	0.5 mm <sup>2</sup>
Conductor cross-section	AWG 20
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

## Commercial data

Packaging size	25
Net weight	1.45 g
Country of origin	Germany
Customs tariff number	85366990

---