

Han Q12-F-QL 1,5mm²



Part number	09 12 012 3104
Specification	Han Q12-F-QL 1,5mm ²
HARTING eCatalogue	https://b2b.harting.com/09120123104

Identification

Category	Inserts
Series	Han [®] Q
Identification	12/0
Specification	With Han-Quick Lock [®] PE contact

Version

Termination method	Crimp termination
Gender	Female
Size	3 A
Number of contacts	12
PE contact	Yes
Details	Black slide Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Electrical data acc. to IEC 61984	10 A 400 V 6 kV 3
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	≥10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0



Pushing Performance

Material properties

RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	11.88 g
Country of origin	Germany
Customs tariff number	85366990