

Han Megabit insert female



| Part number | 09 14 008 3116 |
|--------------------|-------------------------------------|
| Specification | Han Megabit insert female |
| HARTING eCatalogue | https://b2b.harting.com/09140083116 |

Identification

| Category | Inserts |
|---------------|---------------------------------|
| Specification | Han [®] Megabit insert |
| | 2x 4 contacts |
| | 2 cable entries |

Version

| Termination method | Crimp termination |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Gender | Female |
| Number of contacts | 8 |
| Additional contacts | + shielding |
| Details | Please order crimp contacts separately. Please order adapter module separately. |
| Details | Not suitable for hoods/housings low construction as well as Han-Modular [®] Eco, Han-Modular [®] Compact and Han-Modular [®] Twin. |

Technical characteristics

| Conductor cross-section | 0.14 2.5 mm² |
|-----------------------------------|------------------------------|
| Electrical data acc. to IEC 61984 | 10 A 50 V 0.8 kV 3 |
| Rated current | 10 A |
| Rated voltage | 50 V |
| Rated impulse voltage | 0.8 kV |
| Pollution degree | 3 |
| Contact resistance, shielding | ≤10 mΩ |
| Limiting temperature | -40 +85 °C |
| Mating cycles | ≥500 |
| Transmission characteristics | Cat. 5 Class D up to 100 MHz |
| Data rate | 10 Mbit/s 100 Mbit/s |



Material properties

| Material (insert) | Polycarbonate |
|-------------------------------------------|------------------------------|
| Colour (insert) | RAL 7032 (pebble grey) |
| Material (shielding) | Zinc die-cast, nickel-plated |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | е |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| Specifications | EN 60664-1 IEC 61984 |
|----------------|-------------------------|
| Approvals | DNV GL |
| UL / CSA | UL 1977 ECBT2.E102079 |

Commercial data

| Packaging size | 1 |
|-----------------------|----------|
| Net weight | 43.5 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |