

Han E Coax female



Part number	09 15 001 3123
Specification	Han E Coax female
HARTING eCatalogue	https://b2b.harting.com/09150013123

Identification

Category	Inserts
Series	Han [®] E Coax
Description of the contact	for Han E [®] crimp contacts

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	1
Additional contacts	+ shielding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 4 mm ²
Electrical data acc. to IEC 61984	16 A 50 V 0.8 kV 3
Rated current	16 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Contact resistance, shielding	≤10 mΩ
Impedance	50 Ω
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant



Pushing Performance

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	1
Net weight	26.76 g
Country of origin	Germany
Customs tariff number	85389099