

# Han 3 Quintax-F-c



Part number	09 15 003 3101
Specification	Han 3 Quintax-F-c
HARTING eCatalogue	https://b2b.harting.com/09150033101

### Identification

Category	Inserts
Series	Han-Brid <sup>®</sup>
Identification	Han-Brid <sup>®</sup> Quintax 3 A

### Version

Termination method	Crimp termination
Gender	Female
Size	3 A
Number of contacts	1 4 8
Additional contacts	+ shielding + 2 power contacts
Details	Please order contacts separately.

### Technical characteristics

Conductor cross-section	0.14 2.5 mm²
Insulation resistance	≥10 <sup>10</sup> Ω
Limiting temperature	-40 +70 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



# Material properties

# Specifications and approvals

Specifications	EN 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

#### Commercial data

Packaging size	10
Net weight	7.58 g
Country of origin	Germany
Customs tariff number	85366990