

R 15-7+E-ISK-BU



Part number	09 15 007 3121
Specification	R 15-7+E-ISK-BU
HARTING eCatalogue	https://b2b.harting.com/09150073121

Identification

Category	Inserts
Series	R15

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	7
Details	for metal hoods / housings

Technical characteristics

Electrical data acc. to IEC 61984	10 A 250 V 4 kV 3
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	$\geq 10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polyamide
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	HB
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	8.85 g
Country of origin	Germany
Customs tariff number	85389099