

# Han 4A - Female - Quick Lock 1,5mm<sup>2</sup>



Part number	09 20 004 2734
Specification	Han 4A - Female - Quick Lock 1,5mm²
HARTING eCatalogue	https://b2b.harting.com/09200042734

### Identification

Category	Inserts
Series	Han A <sup>®</sup>

### Version

Termination method	Han-Quick Lock <sup>®</sup> termination
Gender	Female
Size	3 A
Number of contacts	4
PE contact	Yes
Details	Black slide

### Technical characteristics

Material properties

Colour (insert)

Conductor cross-section	0.25 1.5 mm²
Electrical data acc. to IEC 61984	10 A 230/400 V 4 kV 3
Rated current	10 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Alternative electrical data	10 A 250 V 4 kV 3
Rated voltage acc. to UL	600 V
Insulation resistance	≥10 <sup>10</sup> Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500

# Material (insert) Polycarbonate

RAL 7032 (pebble grey)



## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

### Commercial data

Packaging size	10
Net weight	15.66 g
Country of origin	Germany
Customs tariff number	85366990