

## Han Yellock multiplier 1:1



Part number	11 05 105 2801
Specification	Han Yellock multiplier 1:1
HARTING eCatalogue	<a href="https://b2b.harting.com/11051052801">https://b2b.harting.com/11051052801</a>

### Identification

Category	Inserts
Series	Han-Yellock®
Element	Multiplier
Specification	0 Bridged contacts 5 Unbridged contacts

### Version

Gender	Female
Number of contacts	5

### Technical characteristics

Insulation resistance	$\geq 10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	$\geq 500$

### Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

## Commercial data

Packaging size	1
Net weight	4.48 g
Country of origin	Germany
Customs tariff number	85366990