

Han Yellock multiplier 2:3



Part number	11 05 105 2802
Specification	Han Yellock multiplier 2:3
HARTING eCatalogue	https://b2b.harting.com/11051052802

Identification

Category	Inserts
Series	Han-Yellock [®]
Element	Multiplier
Specification	2 Bridged contacts 3 Unbridged contacts

Version

Gender	Female
Number of contacts	5

Technical characteristics

Insulation resistance	≥10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 3000 (flame red)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984



Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	1
Net weight	5.24 g
Country of origin	Germany
Customs tariff number	85366990