

Han Yellock multiplier 4:1



Part number	11 05 105 2804
Specification	Han Yellock multiplier 4:1
HARTING eCatalogue	https://b2b.harting.com/11051052804

Identification

Category	Inserts
Series	Han-Yellock®
Element	Multiplier
Specification	4 Bridged contacts 1 Unbridged contacts

Version

Gender	Female
Number of contacts	5

Technical characteristics

Insulation resistance	$\geq 10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 3000 (flame red)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	1
Net weight	7.1 g
Country of origin	Germany
Customs tariff number	85366990