

Han Yellock multiplier 5:0



| | |
|--------------------|---|
| Part number | 11 05 105 2805 |
| Specification | Han Yellock multiplier 5:0 |
| HARTING eCatalogue | https://b2b.harting.com/11051052805 |

Identification

| | |
|---------------|--|
| Category | Inserts |
| Series | Han-Yellock® |
| Element | Multiplier |
| Specification | 5 Bridged contacts 0 Unbridged contacts |

Version

| | |
|--------------------|--------|
| Gender | Female |
| Number of contacts | 5 |

Technical characteristics

| | |
|-----------------------|-----------------------|
| Insulation resistance | $\geq 10^{10} \Omega$ |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥ 500 |

Material properties

| | |
|---|----------------------|
| Material (insert) | Polycarbonate |
| Colour (insert) | RAL 3000 (flame red) |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| | |
|----------------|-------------------------|
| Specifications | EN 60664-1 IEC 61984 |
|----------------|-------------------------|



Pushing Performance

Specifications and approvals

| | |
|-----------|-----------------------|
| Approvals | DNV GL |
| UL / CSA | UL 1977 ECBT2.E235076 |

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 1 |
| Net weight | 5.78 g |
| Country of origin | Germany |
| Customs tariff number | 85366990 |