

## Yellock Monoblock 30 female



Part number	11 05 325 3101
Specification	Yellock Monoblock 30 female
HARTING eCatalogue	<a href="https://b2b.harting.com/11053253101">https://b2b.harting.com/11053253101</a>

### Identification

Category	Inserts
Series	Han-Yellock®
Element	Monoblock

### Version

Termination method	Crimp termination
Gender	Female
Size	Han-Yellock® 30
Number of contacts	25
Details	Please order crimp contacts separately. ATTENTION! It is not possible to use 2 monoblocks 30 in the Han-Yellock® 60 series!

### Technical characteristics

Conductor cross-section	0.14 ... 4 mm <sup>2</sup>
Electrical data acc. to IEC 61984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	≥10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

### Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant



Pushing Performance

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

## Commercial data

Packaging size	2
Net weight	23 g
Country of origin	Germany
Customs tariff number	85389099