

Han Q-Data RJ45-M



Part number	09 12 011 3001
Specification	Han Q-Data RJ45-M
HARTING eCatalogue	https://b2b.harting.com/09120113001

Identification

Category	Inserts
Series	Han [®] Q
Identification	Data RJ45

Version

Termination method	Crimp termination
Gender	Male
Size	Han-Compact [®]
Number of contacts	8
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.13 ... 0.52 mm ²
Electrical data acc. to IEC 61984	5 A 50 V 0.8 kV 3
Rated current	5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	≥10 ¹⁰ Ω
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	1
Net weight	14.92 g
Country of origin	Germany
Customs tariff number	85366990