

Han Multi module, female (DIN)



Part number	09 14 004 4512
Specification	Han Multi module, female (DIN)
HARTING eCatalogue	https://b2b.harting.com/09140044512

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Multi module

Version

Gender	Female
Number of contacts	4
Details	Please order contacts separately.
Details	When removing the contacts, the two-piece module can be opened using a 7mm screwdriver. This destroys the module.

Technical characteristics

Electrical data acc. to IEC 61984	1.5 A 50 V
Rated current	1.5 A
Rated voltage	50 V
Insulation resistance	$\geq 10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Approvals	DNV GL
-----------	--------

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	2
----------------	---

Net weight	7.34 g
------------	--------

Country of origin	Germany
-------------------	---------

Customs tariff number	85389099
-----------------------	----------