

Han Multi module, 12 pin male



Part number	09 14 012 4501
Specification	Han Multi module, 12 pin male
HARTING eCatalogue	https://b2b.harting.com/09140124501

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Multi module
Description of the module	acc. to DIN 41626

Version

Gender	Male
Number of contacts	12
Details	Please order contacts separately.
Details	Due to the closed entry design of female insert the upper part has to be removed by screw driver before extracting the contacts.

Technical characteristics

Electrical data acc. to IEC 61984	1.5 A 50 V
Rated current	1.5 A
Rated voltage	50 V
Insulation resistance	$\geq 10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Approvals	DNV GL
-----------	--------

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	1
----------------	---

Net weight	10.46 g
------------	---------

Country of origin	Germany
-------------------	---------

Customs tariff number	85389099
-----------------------	----------